



See page 36 for details

QE95

95 mm Ø, 15 µJ - 250 J



KEY FEATURES

1. **MODULAR CONCEPT**
Increase the power capability of your detector:
2 different cooling modules
2. **EXTRA LARGE APERTURE**
Effective aperture of 95 mm Ø
3. **QED ATTENUATOR AVAILABLE**
 - Measure up to 5X higher energies
 - Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength
4. **LOW NOISE LEVEL**
15 µJ for the MB coating
5. **TEST TARGET INCLUDED**
With the MB models
6. **SMART INTERFACE**
Containing all the calibration data

AVAILABLE MODELS



QE95LP-S-MB
(Broadband-Convection)



QE95LP-H-MB
(Broadband-Heatsink)



QE95ELP-S-MB
(Long Pulse-Convection)



QE95ELP-H-MB
(Long Pulse-Heatsink)

ACCESSORIES



Stand with Delrin Post
(200428, For -S Model)



Stand with Delrin Post
(201284, For -H Model)



DB-15 to BNC Adaptor
(Model Number: 200036)



QED-95 Attenuator
(Model Number: 201323)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	12
CALIBRATION	6
TECHNICAL DRAWINGS	54
ABSORPTION CURVES	56
QED ATTENUATOR	39
COMPATIBLE MONITORS	
MAESTRO	20
S-LINK	28
M-LINK	32
LIST OF ALL ACCESSORIES	190
APPLICATION NOTE	
LONG PULSE JOULEMETER IN BURST MODE	202153

QE95

SPECIFICATIONS



*Also traceable to NRC-CNRC

	QE95LP-S-MB	QE95LP-H-MB	QE95ELP-S-MB	QE95ELP-H-MB
MAX MEASURABLE ENERGY (WITH ATTENUATOR)	250 J	250 J	250 J	250 J
MAX REPETITION FREQUENCY	40 Hz	40 Hz	10 Hz	10 Hz
EFFECTIVE APERTURE	95 mm Ø	95 mm Ø	95 mm Ø	95 mm Ø

MEASUREMENT CAPABILITY								
Spectral Range *	Alone		Attenuator		Alone		Attenuator	
	0.19 – 20 µm	0.3 - 2.1 µm	0.19 – 20 µm	0.3 - 2.1 µm	0.19 – 20 µm	0.3 - 2.1 µm	0.19 – 20 µm	0.3 - 2.1 µm
Maximum Measurable Energy^{a,b}	Alone		Attenuator		Alone		Attenuator	
1064 nm, 150 µs pulse, Single shot ^c	70 J	250 J	70 J	250 J	70 J	250 J	70 J	250 J
1064 nm, 7 ns, 10 Hz	35 J	150 J	35 J	150 J	35 J	150 J	35 J	150 J
266 nm, 7 ns, 10 Hz	30 J	50 J	30 J	50 J	30 J	50 J	30 J	50 J
Noise Equivalent Energy^d	15 µJ		15 µJ		30 µJ		30 µJ	
Sensitivity^{e,f}	2 V/J		2 V/J		0.6 V/J		0.6 V/J	
Max Repetition Frequency	40 Hz		40 Hz		10 Hz		10 Hz	
Rise Time (typical 0-100 %)	1.5 ms		1.5 ms		5 ms		5 ms	
Maximum Pulse Width (typical)	2 ms		2 ms		6 ms		6 ms	
Calibration Uncertainty^g	±3 %		±3 %		±3 %		±3 %	
Repeatability	<0.5 %		<0.5 %		<0.5 %		<0.5 %	

DAMAGE THRESHOLDS								
Maximum Average Power All Wavelengths	Alone		Attenuator		Alone		Attenuator	
	20 W	45 W	40 W	90 W	20 W	45 W	40 W	90 W
Maximum Energy Density	Alone		Attenuator		Alone		Attenuator	
1064 nm, 150 µs, 10 Hz	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²
1064 nm, 7 ns, single shot	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²
1064 nm, 7 ns, 10 Hz	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²
532 nm, 7 ns, 10 Hz	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²
266 nm, 7 ns, 10 Hz	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²
Maximum Average Power Density (@12 W)	10 W/cm ²	600 W/cm ²	10 W/cm ² ^h	600 W/cm ²	10 W/cm ²	600 W/cm ²	10 W/cm ² ^h	600 W/cm ²

PHYSICAL CHARACTERISTICS								
Effective Aperture (with Attenuator)	95 mm Ø (90 mm Ø)							
Absorber	Multi-Band		Multi-Band		Multi-Band		Multi-Band	
Dimensions	122H x 122W x 20D mm		122H x 122W x 98D mm		122H x 122W x 20D mm		122H x 122W x 98D mm	
Weight	0.78 kg		1.2 kg		0.78 kg		1.2 kg	

ORDERING INFORMATION	Standard	With Attenuator ⁱ	Standard	With Attenuator ⁱ	Standard	Standard
Product Name	QE95LP-S-MB	QE95LP-S-MB-QED	QE95LP-H-MB	QE95LP-H-MB-QED	QE95ELP-S-MB	QE95ELP-H-MB
Product Number (Including stand)	201315	202196	201316	202197	201317	201318
Add Extension for INTEGRA	-INT	-INT	-INT	-INT	-INT	-INT
Product Number (Including stand)	202777	202779	202773	202775	202771	202769

* For the calibrated spectral range, see the user manual.

a. Not exceeding Maximum Average Power.

b. maximum depends on monitor.

c. Increasing pulse width increases the maximum measurable energy.

d. Nominal value, actual value depends on electrical noise in the measurement system.

e. Load: 1 MΩ and ≤ 30 pF.

f. Maximum output voltage = sensitivity x maximum energy.

g. Excludes non-linearities.

h. At 12 W. Maximum Average Power Density is 5 W/cm² @ 40 W

i. When -QED extension is added, the QE + QED come as one unit with a combined calibration only. See the "QED Attenuator" page for more options on the calibration.

Specifications are subject to change without notice